
#### Nanosystems and Technologies GmbH nanopus

## **Distributed Feedback Lasers** 2600 nm - 2900 nm

#### WAVELENGTH

760-830 nm 830–920 nm 920–1100 nm 1100–1300 nm 1300–1650 nm 1650–1850 nm 1850–2200 nm 2200-2600 nm 2600–2900 nm 2800–4000 nm 4000–4600 nm 4600–5300 nm 5300–5800 nm 5800–6500 nm 6000–14000 nm





Any custom wavelength is possible: You tell us what you need and we deliver it. With our patented DFB technology we design any wavelength between 760 nm and 14 µm.

Our excellent spectral purity is characterized by a large side mode suppression ratio (SMSR) of > 35 dB, giving your system a low signal to noise ratio against crossinterference.

A narrow linewidth below 3 MHz guarantees ultra-precise scanning of the absorption line feature. The high output power of several mW yields a stronger signal and increases your measurement precision.

### Fast and wide wavelength tuning is required for in situ

Overgrowth-free DFB device processing

**Key features:** 

MONOMODE

CONTINUOUS WAVE


systems. Most customers use a scan rate of 10 kHz and benefit from our very large tuning coefficient.

#### "Do not change your ideas, let us deliver a laser that fits your application."

We offer various packaging options, e.g. several free space housings including TEC and NTC, fiber coupling, collimation and custom designs. What do you require?

If you require custom specifications, please contact us. Nearly 80 % of our devices are more or less customer-specific. As nanoplus is a fully vertically integrated company, we control the entire process chain from design to packaging. Both nanoplus production facilities are based in Germany. To guarantee consistent product quality we apply a strict and ISO certified quality management system at all levels.


Our sales and R&D teams have long-standing experience in developing lasers. They will advise you in your design and realization phase as well as after-sales: We make market leaders!




TO5 and TO56 packages

# Typical Specifications: 2600 nm - 2900 nm

This data sheet reports performance data of a **sample nanoplus DFB laser at 2740 nm**, which is representative for the entire wavelength range.





Typical room temperature cw spectrum of a nanoplus DFB laser at 2740 nm

Typical mode hop free tuning of a nanoplus DFB laser at 2740 nm by current and temperature

\* non-condensing

electro-optical characteristics	symbol	unit	min.	typ	max.
operating wavelength (at $T_{op},I_{op})$	$\lambda_{_{op}}$	nm		Please specify to 0.1 nm.	
optical output power (at $\lambda_{_{op}}$ )	P <sub>op</sub>	mW		2	
operating current	l <sub>op</sub>	mA		100	
operating voltage	$V_{_{op}}$	V		2.3	
threshold current	l <sub>th</sub>	mA	30	50	80
side mode suppression ratio	SMSR	dB		> 35	
current tuning coefficient	C,	nm / mA	0.01	0.02	0.05
temperature tuning coefficient	C <sub>T</sub>	nm / K	0.15	0.20	0.28
operating chip temperature	T <sub>op</sub>	°C	+20	+25	+50
operating case temperature*	T <sub>c</sub>	°C	-20	+25	+50
storage temperature*	Τ <sub>s</sub>	°C	-40	+20	+80

### laser packaging options

TO5 with TEC and NTC, black cap, AR coated window TO56 without TEC or NTC, sealed, window

c-mount without TEC or NTC

chip on carrier without TEC, with NTC

Technical drawings & accessories are available at: https://nanoplus.com/packaging-options

Please contact <u>sales@nanoplus.com</u> for customized specifications, quotes and further questions. Visit our website for technical notes, application samples or literature referrals. nanoplus Nanosystems and Technologies GmbH, www.nanoplus.com, phone: +49 (0) 3693 50 5000-0, email: sales@nanoplus.com °copyright nanoplus Nanosystems and Technologies GmbH 2020, all rights reserved. Technical data is subject to change without notice.

Rev.DFB2740.12